Multi-core Planar Tube

Characteristics

- This flexible, multi-core tube is made of polyurethane (UQ) or soft polyurethane (UCQ).
- The multi-core tube is suitable for air supply to multiple drives.
- For the black 2 core tube, the discernment line is printed on one tube to prevent a piping mistake.
- The useful cut marks on every 500mm are printed.
- Tubes with 3-6 Cores, different type of Arrangement (Parallel or Pyramid Type) and 10-Color Selection are available as make-to-order products.

Specifications of UQ

Model		UQ03	UQ04	UQ06	UQ08	UQ10	UQ12			
9	O.D.×I.D. (mm)	3×2	4×2.5	6×4	8×5	10×6.5	12×8			
Size	Tube length (m)		20 · 100							
	Black (B)		: available							
	Red (R)			Δ	×2					
	Orange (O)			Δ	×2					
~	Ocher (YB)	△ *2								
color	Yellow (Y)	△ *2								
Tube	Green (G)	△ *2								
F	Blue (BU)		△ *2							
	Clear blue (CB)		△ *2							
	Transparent (C)	△ *2								
	Milky white (W)	△ *2								
Flu	iid medium	Air								
Ma	k. operating pressure	116psi (0.8MPa) (65%RH at 20°C *1)								
Ma	x. vacuum	-29.5 in. Hg (-100 kPa)								
Ор	erating temp. range	-5 ~ 140°F (-15 ~ 60°C) (no freezing)								
*1 7	*1. The value of may operating pressure is measured at 20°C and 65% RH. When Tubes are used in different condi-									

Specifications of UCQ

Model		UCQ04	UCQ06	UCQ08	UCQ10	UCQ12				
Size	O.D.×I.D. (mm)	4×2.5	6×4	8×5	10×6.5	12×8				
S	Tube length (m)		20 · 100							
	Clear black (CBL)			0						
(age)	Clear orange (CO)		0							
Tube color (0: available)	Clear yellow (CY)	0								
) Jugo	Clear green (CG)	Ö								
Tibe	Clear blue (CB)		0							
	Transparent (C)	0								
Flu	iid medium			Air						
Max	x. operating pressure	87 psi (0.6 MPa) (65%RH at 20°C *1)								
Max. vacuum		-29.5 in. Hg (-100 kPa)								
Ор	erating temp. range	-5 ~ 140°F (-15 ~ 60°C) (no freezing)								

are frequently swung and bent, there is a possibility of generating heat between molecules and damaging the products.

Model Designation (Example)



(1) Tube type

UQ: Multi-core Planar Tube UCQ: Soft Multi-core Planar Tube

(2) Tube dia. (O.D./I.D.)

	mm size							
Code	03*	04	06	08	10	12		
O.D.	ø3mm	ø4mm	ø6mm	ø8mm	ø10mm	ø12mm		
I.D. ø2mm		ø2.5mm	ø4mm	ø5mm	ø6.5mm	ø8mm		

^{*} Tube O.D. ø3mm is available only for UQ type

(3) No. of cores

Code	2F	3F*	4F *	5F *	6F *
Core	2 cores	3 cores	4 cores	5 cores	6 cores

^{* 3-6} cores of equal tube dia. are available as a make-to-order product.

(1) Tabo longar							
Code	20	100					
Length	20m	100m					

^{*} Other length is available as a make-to-order product. Refer to the right table

■ Tube dia. and max. length of each tube core (Unit: m)

Tube O.D. No. of core	ø3mm	ø4mm	ø6mm	ø8mm	ø10mm	ø12mm
2	100	100	100	100	100	100
3	100	100	100	100	80	65
4	100	100	100	75	60	50
5	100	100	80	60	50	40
6	100	100	65	50	40	30

(5), (6), (7), (8), (9), (10) Tube color

■ UQ

Code	В	R	0	YB	Υ	G	BU	CB	С	W
color	Black	Red	Orange	Ocher	Yellow	Green	Blue	Clear blue	Transparent	Milky white
UCQ										


ĺ	Code	CBL	CO	CY	CG	СВ	С
	color	Clear black	Clear orange	Clear yellow	Clear green	Clear blue	Transparent

Tube color 1 Tube color 2 *Color combinations other than black are available as make-to-order products.

^{*2.} Color selection with marking \triangle is available as a make-to-order product.

Producible core numbers & arrangement as make-to order products


Equal tube dia. Parallel arrangement: 3-6 cores
 3 cores **000** 4 cores **0000** 5 cores 00000 6 cores



Unequal tube dia. (Special-made)
• 2 and 3 cores only (Parallel arrangement only)



Burst Pressure Curve (Reference Value)



Detailed Safety Instructions

Before using the PISCO products, be sure to read the "Safety Instructions", "Common Safety Instructions for Products in This Catalog" on page 13 to 16 and "Common Safety Instructions for Tubes" on page 66.

△Caution: 1. When the tubes are difficult to split into each core, cut the tube edge between each core around 5mm with a cutter.

The products listed in this page are ECO-friendly products.

* Please refer to page 4 for the details of ECO-friendly products.

Thouse force to page	ge 4 for the details of ECO-mendiy	Siodabio.	
UQ	Model code	UCQ	Model code
2 Core Planar Tube	UQ03-2F-4-5-6	2 Core Soft Planar Tube	UCQ04-2F-4-5-6
	UQ04-2F-4-5-6		UCQ06-2F-4-5-6
	UQ06-2F-4-5-6		UCQ08-2F-4-5-6
	UQ08-2F-4-5-6		UCQ10-2F-4-5-6
	UQ10-2F-4-5-6		UCQ12-2F-4-5-6
	UQ12-2F-4-5-6	, ,	
UQ	Model code	UCQ	Model code
3 Core Planar Tube	UQ03-3F-4-5-6-7	3 Core Soft Planar Tube	UCQ04-3F-4-5-6-7
	UQ04-3F-4-5-6-7		UCQ06-3F-4-5-6-7
	UQ06-3F-4-5-6-7		UCQ08-3F-4-5-6-7
	UQ08-3F-4-5-6-7		UCQ10-3F-4-5-6-7
	UQ10-3F-4-5-6-7		UCQ12-3F-4-5-6-7
	UQ12-3F-4-5-6-7	, , , , , , , , , , , , , , , , , , ,	
UQ	Model code	UCQ	Model code
4 Core Planar Tube	UQ03-4F-4-5-6-7-8	4 Core Soft Planar Tube	UCQ04-4F-4-5-6-7-8
	UQ04-4F-4-5-6-7-8		UCQ06-4F-4-5-6-7-8
	UQ06-4F-4-5-6-7-8		UCQ08-4F-4-5-6-7-8
	UQ08-4F-4-5-6-7-8		UCQ10-4F-4-5-6-7-8
	UQ10-4F-4-5-6-7-8		UCQ12-4F-4-5-6-7-8
•	UQ12-4F-4-5-6-7-8		
UQ	Model code	UCQ	Model code
5 Core Planar Tube	UQ03-5F-4-5-6-7-8-9	5 Core Soft Planar Tube	UCQ04-5F-4-5-6-7-8-9
	UQ04-5F-4-5-6-7-8-9		UCQ06-5F-4-5-6-7-8-9
	UQ06-5F-4-5-6-7-8-9		UCQ08-5F-4-5-6-7-8-9
	UQ08-5F-4-5-6-7-8-9		UCQ10-5F-4-5-6-7-8-9
	UQ10-5F-4-5-6-7-8-9		UCQ12-5F-4-5-6-7-8-9
	UQ12-5F-4-5-6-7-8-9		
UQ	Model code	UCQ	Model code
6 Core Planar Tube	UQ03-6F-4-5-6-7-8-9-10	6 Core Soft Planar Tube	
	UQ04-6F-4-5-6-7-8-9-10		UCQ06-6F-4-5-6-7-8-9-10
	UQ06-6F-4-5-6-7-8-9-10		UCQ08-6F-4-5-6-7-8-9-10
	UQ08-6F-4-5-6-7-8-9-10		UCQ10-6F-4-5-6-7-8-9-10
	UQ10-6F-4-5-6-7-8-9-10		UCQ12-6F-4-5-6-7-8-9-10
	UQ12-6F-4-5-6-7-8-9-10	8	



- * 4]: Replaced with Tube length
 * 5, 5, 7, 8, 9, 10: Replaced with Tube color code.
 * The combination of Black color with 2 cores is the only standard item and the other colors are available as a make-to-order



Package specification

20M lengths /bag: Applicable to all types

100M lengths /box: Applicable to Tubes that are available in 100m. Refer to "Tube dia. and max. length" table on previous page.